

SKINDICHT® DTN

SKINDICHT® DTN, duct, can be used as multiple-duct sleeve, with strain relief, for cables from 4-32mm cable diameter



Optimum strain relief

Benefits

Can be used as multiple-duct sleeve
Strain relief

Application range

Grommets for cables from 4 to 32 mm cable diameter.

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000879

ETIM 5.0 Class-Description: Feed through spout

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000879

ETIM 6.0 Class-Description: Feed through spout

Colour delivered:

Black

Material:

CR

Temperature range:

-30 °C to +100 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® DTN

Article number	Article designation / size	Ø F mm	Metal thickness (mm)	Hole in housing Ø (mm)	Sleeve inner Ø (mm)	Pieces / PU
SKINDICHT® DTN						
52105020	DTN 1	4.0 - 9.0	2.5	16	9	50
52105030	DTN 2	7.0 - 12.0	2.5	19	12	50
52105040	DTN 3	12.0 - 17.5	2.5	25	18	50
52105050	DTN 4	18.0 - 23.0	2.5	32	25	25
52105060	DTN 5	25.0 - 29.0	3.0	38	32	25