

SKINDICHT® LA

SKINDICHT® LA, duct, as protection against sharp or angular housing walls, easy to assemble, for control cabinet manufacturing



Reliability

Benefits

Protection against sharp or angular housing walls
Easy to assemble

Application range

Housings
Control cabinet manufacturing

Note

Simply push the grommet into the hole until the groove engages.

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000879

ETIM 5.0 Class-Description: Feed through spout

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000879

ETIM 6.0 Class-Description: Feed through spout

Colour delivered:

Black

Material:

CR

Temperature range:

-30 °C to +90 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® LA

Article number	Article designation / size	Metal thickness (mm)	Sleeve outer Ø (mm)	Hole in housing Ø (mm)	Sleeve inner Ø (mm)	Pieces / PU
SKINDICHT® LA						
61713520	LA 3	1.5 - 2.0	10	7	3	100
61713530	LA 4	1.5 - 2.0	11	8	4	100
61713540	LA 5	1.5 - 2.0	11	7	5	100
61713550	LA 6	1.5 - 2.0	14	9	6	100
61713560	LA 7	1.5 - 2.0	16	12	7	100
61713570	LA 8	1.5 - 2.0	15	11	8	100
61713580	LA 9	1.5 - 2.0	16	11	9	100
61713590	LA 11	1.5 - 2.0	19	14	11	100
61713600	LA 12	1.5 - 2.0	25	18	12	100