

SKINDICHT® SNR

SKINDICHT® SNR, anti-kink sleeves for improved protection against kinking



Benefits

Alternative anti-kink sleeves

Application range

Anti-kink sleeves for improved protection against kinking in SKINDICHT® cable glands.

Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000451 ETIM 5.0 Class-Description: Cable plug sealing clamp
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000451 ETIM 6.0 Class-Description: Cable plug sealing clamp
Colour delivered:	Black
Material:	CR
Temperature range:	-20°C to +80°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® SNR

Article number	External/internal PG size	Max. cable Ø (mm)	Min. cable Ø (mm)	Pieces / PU
SKINDICHT® SNR				
52001970	7/ 5.0	5	3.5	100
52001980	9/ 7.0	7	5.5	100
52001990	11/ 7.0	7	5.5	100
52002000	11/ 9.0	9	7.5	100
52002010	13.5/ 9.0	9	7.5	100
52002020	13.5/ 11.0	11	9	100
52002030	13.5/ 13.0	13	11	100
52002040	16/ 13.0	13	11.5	100
52002050	16/ 15.0	15	13	100
52002060	21/ 15.0	15	13.5	50
52002070	21/ 17.0	17	15	50
52002080	21/ 19.0	19	17	50
52002090	21/ 20.0	20	18	50
52002100	29/ 20.0	20	18	25
52002110	29/ 23.0	23	21	25
52002120	29/ 25.0	25	23	25
52002130	36/ 26.0	26	23	25
52002140	36/ 30.0	30	27	25
52002150	36/ 33.0	33	30	25
52002160	36/ 35.0	35	32	25
52002170	42/ 35.0	35	32	10
52002180	42/ 38.0	38	35	10
52002190	42/ 40.0	40	36	10
52002200	48/ 40.0	40	36	10
52002210	48/ 44.0	44	40	10