

## SKINTOP® ST-M L-BOXX

Being organised is essential. With our product case for SKINTOP® ST-M cable glands with a component insert and transparent lid, you always have the right thread size at hand. Thanks to its robust design, integration in vehicle equipment systems and the snap-in system for combination with other cases, it is perfectly suited for assembly use.



### Benefits

Inset for loose components ensures optimum organisation and prevents mixing of the items.

Case made of light and robust, shock- and impact-resistant ABS plastic.

Intelligent snap system allows quick connection, combination and disconnection of cases, saving time and energy during transport.

Easy integration in vehicle equipment systems of numerous manufacturers.

Transparent lid allows a perfect overview even when closed.

### Application range

For safe transport and storage of SKINTOP® ST-M cable glands (sizes M12 to M32).

Especially for assembly use, e.g. on the construction site.

### Product features

Two robust locking mechanisms ensure a secure closure.

Case can be refilled with standard packaging units.

Mounting instruction and locknut included.

### Included

SKINTOP® ST-M M12 / 50 pieces

SKINTOP® ST-M M16 / 50 pieces

SKINTOP® ST-M M20 / 25 pieces

SKINTOP® ST-M M25 / 25 pieces

SKINTOP® ST-M M32 / 5 pieces

Counter nut SKINTOP® GMP-GL-M included

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 Class-Description: Cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class-Description: Cable screw gland

Colour delivered:

Silver grey (RAL 7001)

Light grey (RAL 7035)

Black (RAL 9005)

Last Update (09.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SKINTOP® ST-M L-BOXX

**Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINTOP® ST-M L-BOXX**

Article number	Article designation / size	Ø F mm	PU
53110050	SKINTOP® ST-M L-BOXX (SGY)	-	1
53110051	SKINTOP® ST-M L-BOXX (LGY)	-	1
53110052	SKINTOP® ST-M L-BOXX (BK)	-	1