

EPIC® H-D 1.6 stamped contacts


For inserts and modules of the EPIC® rectangular connectors

With H-D 1.6 pressed contacts, handling is easy using the removal tool, crimping pliers and locator.

Info

Choice of high quality gold or silver plated contacts

Two crimp areas with wire and insulation crimp



Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 Class-Description: Contact for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-D 1.6 stamped contacts

Article number	Article description	Contact type	Conductor cross-section (mm ²)	Surface	Stripping length (mm)	Pieces / PU
Contacts						
11241100	H-D 1.6 stamped	male	0.14 - 0.5	Ag	3,0	100
11231100	H-D 1.6 stamped	female	0.14 - 0.5	Ag	3,0	100
11221000	H-D 1.6 stamped	male	0.5 - 1.5	Ag	4,0	100
11236100	H-D 1.6 stamped	female	0.5 - 1.5	Ag	4,0	100
11223500	H-D 1.6 stamped	male	1.5 - 2.5	Ag	4,0	100
11228500	H-D 1.6 stamped	female	1.5 - 2.5	Ag	4,0	100
11243100	H-D 1.6 stamped	male	0.14 - 0.5	Au	3,0	100
11233100	H-D 1.6 stamped	female	0.14 - 0.5	Au	3,0	100
11221300	H-D 1.6 stamped	male	0.5 - 1.5	Au	4,0	100
11238100	H-D 1.6 stamped	female	0.5 - 1.5	Au	4,0	100