

EPIC® H-A 3 TS

Innovative metal and plastic housing design

The robust compact plastic housing has a side cable entry and is suitable for use in machine and device manufacturing.

Info

Lightweight, chemically resistant plastic housing

Protection rating UL50E tested



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

Housing in plastic or metal version for safe connections in the smallest possible space

Application range

Machine and equipment manufacturing

Control engineering

Electronic laboratory

Product features

Hood

Bolts for single lever

Side cable entry

Versions with / without cable gland

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-A 3 TS

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	thermoplastic, grey, black Lever: zinc-plated steel
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-A 3 TS

Article number	Article description	M	PG	Material	Colour	Cable gland	Cable clamping range	Pieces / PU
10427300	H-A 3 Ts	-	11	Thermoplastic	black	-	-	10
10427000	H-A 3 Ts	-	11	Thermoplastic	grey	-	-	10
10620600	H-A 3 Ts	-	11	Thermoplastic	black	yes	6.5 - 12	10
10427100	H-A 3 Ts	-	11	Thermoplastic	grey	yes	6.5 - 12	10
19427300	H-A 3 MTSV 7-13	20	-	Thermoplastic	black	-	-	10
19427000	H-A 3 MTSV 7-13	20	-	Thermoplastic	grey	-	-	10

EPIC® H-A 3 TS

