

EPIC® H-B 16 TGH-RO

Housing design H-B. The industry standard.

The robust metal housing with a direct cable entry and pivots for a single lever is available in a version with or without a neck.

Info

Non-slip ridges for comfortable disconnecting

Protection rating UL50E tested

High version: More interior space for wiring



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

The housing standard. Wide choice for all applications

More interior space for wiring

M40 housing extension on M50 with SKINTOP 53112083 possible (clamping range 27 - 35 mm)

Application range

Plant engineering

Light & sound technology

Plastics industry

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 16 TGH-RO

Product features

Hood, high version
Reels for single lever
Straight cable entry
Versions with / without neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) UL50 Type 12 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 16 TGH-RO

Article number	Article description	M	PG	Neck	Pieces / PU
H-B housing: hood (straight cable entry, bolts for single lever, high version)					
70094200	H-B 16 TGH-RO 21	-	21	yes	5
70094400	H-B 16 TGH-RO 29	-	29	yes	5
79094200	H-B 16 TGH-RO M25	25	-	-	5
79094400	H-B 16 TGH-RO M32	32	-	-	5
79094600	H-B 16 TGH-RO M40	40	-	-	5