



EPIC® H-B 32 SGRL

Housing design H-B for 2 inserts.

This connector housing with 2 double levers and 2 cable entries can be used in investment construction and the plastics industry.



Benefits

Two inserts in one housing. With two levers for high safety

M40 housing extension on M50 with SKINTOP 53112083 possible (clamping range 27 - 35 mm)

Application range

Plant engineering

Control engineering

Plastics industry

Product features

Surface-mount base

Dual levers

2 cable entries

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000437

ETIM 5.0 Class-Description: Housing for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000437

ETIM 6.0 Class-Description: Housing for industrial connectors

Material:

Housing: powder-coated aluminium alloy, grey

Lever: zinc-plated steel

Sealing: NBR

Protection rating:

IP 65 (latched)

Temperature range:

-40°C to +100°C, short-term up to +125°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 32 SGRL

Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 32 SGRL

Article number	Article description	M	PG	Pieces / PU
H-B housing: surface-mount base (2 cable entries, double lever)				
10138000	H-B 32 SGRL 29	-	29	5
19138000	H-B 32 SGRL M32	32	-	5
19145400	H-B 32 SGRL M40	40	-	5