

ÖLFLEX® PLUG CEE connecting cable with phase shifter*

H07RN-F-based CEE connecting cable with phase shifter for three-phase current

ÖLFLEX® PLUG CEE connecting cable with phase shifter, <HAR> H07RN-F, plug, three-phase current/ 5-pole, CEE, one-end dismantled

Info

Formerly: ÖLFLEX PLUG CEE (400 V) Connection / Extension Cable



Application range

For connections to any three-phase A.C. consumers

Machines and systems on building sites

According to EN 50565-2: Dry or damp rooms as well as outdoors

Product features

Other dimensions, lengths, connectors, designs and customised versions are available upon request

Norm references / Approvals

<HAR> H07RN-F cable type approval according to EN 50525-2-21

Product Make-up

Mounted 5-pin CEE plug, 400 V, red, 6 o'clock in accordance with VDE 0623/EN 60309-2, splash-proof IP 44

80 mm stripped, with conductor end sleeves

from 10 mm²: 100 mm stripped, with conductor end sleeves

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001576

ETIM 5.0 Class-Description: Power cord

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001576

ETIM 6.0 Class-Description: Power cord

Core identification code:

According to VDE 0293-308 (table T9)

Last Update (28.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® PLUG CEE connecting cable with phase shifter*

Conductor stranding:	Fine wire according to VDE 0295 Class 5/ IEC 60228 Class 5
Nominal voltage:	$U_0/U = 200/346$ to $240/415$
Test voltage:	2500 V
Temperature range:	Flexible use: -25°C to $+60^{\circ}\text{C}$

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

* Trade product, no Lapp product

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Please observe the safety information as per DIN VDE 0620-1, Plugs and socket-outlets for household and similar purposes - Part 1: General requirements, appendix E: "Installation only by persons with the relevant electrotechnical expertise and experience!"

ÖLFLEX® PLUG CEE connecting cable with phase shifter*

Article number	Plug amps	Article designation	Number of cores and mm ² per conductor	Outer diameter [mm]	Length (m)	Copper index kg/1.000 pieces	Weight
71002843	16	H07RN-F	5 G 1.5	11.2 - 14.4	3.5	252	872
71002844	16	H07RN-F	5 G 1.5	11.2 - 14.4	5	360	1170
71002846	16	H07RN-F	5 G 2.5	13.3 - 17	3.5	420	1194
71002847	16	H07RN-F	5 G 2.5	13.3 - 17	5	600	1880