

AHI assorted boxes

Insulated DIN conductor end sleeves for several diameters in a box



Halogen-free

Benefits

Convenient assortment boxes - several diameters always at your fingertips

Norm references / Approvals

The insulated conductor end sleeves are in accordance with DIN 46228, part 4 (0.25 mm² and 0.34 mm² not standardised) in assortment boxes

Product Make-up

AHI assortment box I (yellow):

30 x 0.25 - 6 mm LBU, 30 x 0.34 - 6 mm TQ, 30 x 0.5 - 8 mm ON, 30 x 0.75 - 8 mm WH, 30 x 1.00 - 8 mm YE

AHI assortment box II (orange):

50 x 0.5 - 8 mm OG, 100 x 0.75 - 8 mm WH, 100 x 1.00 - 8 mm YE, 100 x 1.5 - 8 mm RD, 50 x 2.5 - 8 mm BU

AHI assortment box III (blue):

50 x 4.00 - 10 mm GY, 20 x 6.0 - 12 mm BK, 20 x 10.00 - 12 mm WH, 10 x 16.00 - 12 mm GN

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000524

ETIM 5.0 Class-Description: Assortment box for installation- and connection material

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000524

ETIM 6.0 Class-Description: Assortment box for installation- and connection material

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

AHI assorted boxes

| Article number | Article designation | For mm ² | Suitable crimp insert | Contents (unit) | PU |
|--------------------|------------------------|---------------------|-------------------------|-----------------|----|
| AHI assortment box | | | | | |
| 61794720 | AHI assortment box I | 0.25 - 1 | PEW 12.090 | 150 x 1 | 1 |
| 61794730 | AHI assortment box II | 0.5 - 2.5 | PEW 12.090 | 400 x 1 | 1 |
| 61794740 | AHI assortment box III | 4 - 16 | PEW 12.090 / PEW 12.091 | 100 x 1 | 1 |