

## DSA 0110 + DSA 0725 crimping pliers

DSA 0110 and DAS 0725: Crimping pliers for pressing insulated connectors as insulated cable lugs and blade/panel connectors from 0,1 to 1,5 mm<sup>2</sup> and 0,5-2,5 mm<sup>2</sup>



Reliability

### Benefits

- Suitable for left and right-handed users
- Less force required for perfect pressing
- Clearly marked press moulds
- Cross-section of press matrix is embossed in the cable lugs for checking
- Pressing according to the forced finish system

### Application range

- Safety pressing pliers for insulated connections
- For insulated cable lugs, blade connectors and other connectors

### Product features

- Emergency release, if the pressing operation needs to be interrupted

### Norm references / Approvals

- Tested in accordance with DIN standards

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000168

ETIM 5.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000168

ETIM 6.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

General:

Adjustable crimping pressure

Note:

Crimping profile: Oval

### Note

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## **DSA 0110 + DSA 0725 crimping pliers**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**DSA 0110 + DSA 0725 crimping pliers**

Article number	Article designation	For mm <sup>2</sup>	Weight (kg)	Length (mm)	Pieces / PU
61722050	DSA 0110	0.1 - 1.5	0.35	225	1
61722060	DSA 0725	0.5 - 2.5	0.35	192	1