

Panel connectors with latch

Non-insulated Panel connectors/blade connectors with latch, male and female, made of brass



Benefits

For electrical connection of different components

Note

The choice of the correct tool is depending on the cross-section of the conductor and on the blade connection

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000516 ETIM 5.0 Class-Description: Round plug/flat receptacle
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000516 ETIM 6.0 Class-Description: Round or flat plug/receptacle
Material:	BM 638 M + B 638 F: brass blank BM-C 638 M + B-C 638 F: brass tinned
Temperature range:	Type M: max. +90 °C Type F: max. +110 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Panel connectors with latch

Article number	Article designation	For mm ²	UL certification	Blade connection	I	L	Suitable crimp insert	Pieces / PU
Blade connector with locking notch (type M)								
63501020	BM 638 M	1 - 2.5	no	6.3 x 0.8	16	28	PEW 12.050	100
63501022	BM-C 638 M	4 - 6	no	6.3 x 0.8	16	28	PEW 12.751	100
Blade receptacle with locking notch (type F)								
63501010	B 638 F	1.5 - 2.5	no	6.3 x 0.8	7.5	19	PEW 12.465	100
63501012	B-C 638 F	4 - 6	no	6.3 x 0.8	7.5	19	PEW 12.751	100