

## KNIPEX Diagonal cutter

KNIPEX X-Cut® Diagonal cutter with insulated handle for precise cutting

### Info

Narrow head style for use in confined areas



### Benefits

High ergonomics thanks to multi-component handles  
Insulated handles allow working under voltage up to 1000V

### Application range

For soft and hard wire

### Product features

Precision ground, hardened blades

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000142

ETIM 5.0 Class-Description: Cable shears

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000142

ETIM 6.0 Class-Description: Cable shears

Certifications:

Insulated according to IEC 60900, applicable up to 1000V AC / 1500V DC

VDE-tested

Material:

Vanadium steel, forged, multi stage oil-hardened

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

## KNIPEX Diagonal cutter

Article number	Article designation	Soft wire mm	Medium hard wire mm	Hard wire mm	Weight (kg)	Length (mm)
KNIPEX Diagonal cutter						
62120520	Diagonal cutter SESI 16	4	3	2	0.216	160