

SKINDICHT® D-M

SKINDICHT® D-M, nickel-plated brass compression screws with thread in accordance with EN 62444



Application range

SKINDICHT® D-M compression screws with thread in accordance with EN 62444.

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000814

ETIM 5.0 Class-Description: Threaded bush

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000814

ETIM 6.0 Class-Description: Threaded bush

Material:

Nickel-plated brass

Temperature range:

-60 °C to +200 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® D-M

Article number	Article designation / size	SW wrench size mm	Pieces / PU
SKINDICHT® D-M			
52100600	M 12 x 1,5	12	100
52100601	M 16 x 1,5	16	100
52100602	M 20 x 1,5	20	100
52100603	M 25 x 1,5	25	50
52100604	M 32 x 1,5	32	25
52100605	M 40 x 1,5	40	25
52100606	M 50 x 1,5	50	10
52100607	M 63 x 1,5	65	10

Last Update (20.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16