

## SKINDICHT® E-M

SKINDICHT® E-M, incised sealing rings, one seal for several clamping ranges, rings can be individually adapted to various cable diameters



### Benefits

One seal for several clamping ranges

The various incisions can be easily taken out with a knife.

### Application range

Incised sealing ring for SKINDICHT® cable glands

### Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001181

ETIM 5.0 Class-Description: Sealing ring

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001181

ETIM 6.0 Class-Description: Sealing ring

Colour delivered:

Black

Material:

CR

Temperature range:

-20°C to +80°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINDICHT® E-M**

Article number	Article designation / size	Outer Ø x holes (mm)	Thickness (mm)	Pieces / PU
SKINDICHT® E-M				
52100620	E-M 12	10.0 x 5	5.0	250
52100621	E-M 16	13.8 x 3/6/9	5.5	250
52100622	E-M 20	17.6 x 4/7/10/13	6.0	250
52100623	E-M 25	22.6 x 8.5/11.5/14.5/17.5	7.5	100
52100624	E-M 32	29.6 x 16/19/22/25	9.5	100
52100625	E-M 40	37.6 x 23/26/29/32	12.0	50
52100626	E-M 50	47.6 x 30/33/36/39	12.0	50
52100627	E-M 63	60.6 x 36/39/42/45	14.0	50