

SKINDICHT® O-ring FKM metric

SKINDICHT® O-ring FKM metric, sealing ring, to protect against oils, acids, chemicals at parts under extreme conditions



Good chemical resistance



Acid-resistant



Temperature-resistant

Application range

For sealing the housing reliably to protect against oils, acids, and chemicals at the connection thread of a gland or other similar parts under extreme conditions

Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical Data

| | |
|------------------------|---|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC001181 ETIM 5.0 Class-Description: Sealing ring |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC001181 ETIM 6.0 Class-Description: Sealing ring |
| Colour delivered: | Green |
| Material: | FKM |
| Temperature range: | -20 °C to +200 °C |

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® O-ring FKM metric

| Article number | Article designation / size | Inner Ø (mm) | Cable thickness (mm) | Pieces / PU |
|------------------------------|----------------------------|--------------|----------------------|-------------|
| 52122001 | M 12 x 1,5 | 9.0 | 1.5 | 100 |
| SKINDICHT® O-ring FKM metric | | | | |
| 52122000 | M 12 x 2,0 | 9.0 | 2 | 100 |
| 52122010 | M 16 x 2,0 | 13.0 | 2 | 100 |
| 52122021 | M 20 x 1,5 | 17.0 | 1.5 | 100 |
| 52122020 | M 20 x 2,0 | 17.0 | 2 | 100 |
| 52122030 | M 25 x 2,0 | 22.0 | 2 | 100 |
| 52122040 | M 32 x 2,0 | 28.0 | 2 | 50 |
| 52122050 | M 40 x 2,0 | 36.0 | 2 | 50 |
| 52122060 | M 50 x 2,0 | 46.0 | 2 | 25 |
| 52122070 | M 63 x 2,0 | 57.0 | 2 | 25 |