

SKINDICHT® EH

SKINDICHT® EH, alternative brass earthing sleeves for SKINDICHT SHVE and SKINDICHT SRE



Interference signals

Benefits

Alternative earthing sleeves

Application range

Earthing sleeve for SKINDICHT® SHVE and SKINDICHT® SRE.

Note

Allocation example, earthing sleeve for suitable gland

SKINDICHT® EH13.5/5 fits SKINDICHT® SHVE 13.5/9/9/5.

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002317

ETIM 5.0 Class-Description: Earthing lug for cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002317

ETIM 6.0 Class-Description: Earthing lug for cable screw gland

Material:

Brass

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® EH

Article number	PG size/clear opening	Inner Ø (mm)	Flange Ø (mm)	Length (mm)	Pieces / PU
SKINDICHT® EH					
52010980	EH 9 / 3.2	3.2	13.3	11.0	100
52010985	EH 9 / 3.6	3.6	13.3	11.0	100
52010996	EH 11 / 4.5	4.5	16.7	9.0	100
52010000	EH 13.5 / 5	5	18.5	14.0	100
52010010	EH 13.5 / 6	6	18.5	14.0	100
52010020	EH 13.5 / 7	7	18.5	14.0	100
52010030	EH 16 / 8	8	20.5	14.0	50
52010040	EH 16 / 9	9	20.5	14.0	50
52010050	EH 16 / 10	10	20.5	14.0	50
52010060	EH 16 / 11	11	20.5	14.0	50
52010070	EH 21 / 12	12	26	16.0	50
52010080	EH 21 / 13	13	26	16.0	50
52010090	EH 21 / 14	14	26	16.0	50
52010100	EH 21 / 15	15	26	16.0	50
52010110	EH 21 / 16	16	26	16.0	50
52010120	EH 29 / 17	17	35	18.0	25
52010130	EH 29 / 18	18	35	18.0	25
52010140	EH 29 / 19	19	35	18.0	25
52010161	EH 36 / 22	22	45	10.0	10
52010162	EH 36 / 24	24	45	10.0	10
52010163	EH 36 / 26	26	45	10.0	10
52010164	EH 36 / 28	28	45	10.0	10