

SKINDICHT® E

SKINDICHT® E, CR incised sealing ring for several clamping ranges, rings can be individually adapted to various cable diameters



Benefits

One seal for several clamping ranges

The various incisions can be easily taken out with a knife.

Application range

Incised sealing ring for SKINDICHT® cable glands

Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001181

ETIM 5.0 Class-Description: Sealing ring

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001181

ETIM 6.0 Class-Description: Sealing ring

Colour delivered:

Black

Material:

CR

Temperature range:

-20 °C to +80 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® E

Article number	Article designation / size	Outer diameter x bores (mm)	Thickness (mm)	Outer Ø (mm)	Pieces / PU
SKINDICHT® E					
52005780	E 9	13.5 x 5/8	5.5	13.5	250
52003690	E11	16.5 x 7/10/12.5	6.0	16.5	250
52003700	E 13,5	18.5 x 7/10.5/13/16	6.5	18.5	250
52003710	E 16	20.5 x 8/10.5/13.5/16	7.5	20.5	250
52003720	E 21	26.0 x 11/15/18/20	8.0	26.0	100
52003730	E 29	35.0 x 19/23/27/31	9.5	35.0	100
52003740	E 36	45.0 x 25/28/31/35	12.0	45.0	50
52005790	E 42	52.0 x 35.5/39/42.5/46	14.0	52.0	50
52005800	E 48	57.0 x 40.5/44/47/50.5	14.0	57.0	50