

SKINDICHT® O-Ring NBR PG

SKINDICHT® O-Ring NBR PG, sealing ring, resistant to oil, dust and water, for a reliable sealing, ozone and UV-resistant, PG thread



UV-resistant

Benefits

Resistant to oil, dust and water

Application range

For a reliable sealing against foreign objects and liquids at the connecting thread of a gland or similar components.

Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical Data

| | |
|------------------------|---|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC001181 ETIM 5.0 Class-Description: Sealing ring |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC001181 ETIM 6.0 Class-Description: Sealing ring |
| Colour delivered: | Black |
| Material: | NBR |
| Temperature range: | -20°C to +100°C |

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® O-Ring NBR PG

| Article number | Article designation / size | Inner Ø x thickness Ø (mm) | Pieces / PU |
|-----------------------|----------------------------|----------------------------|-------------|
| SKINDICHT® O-Ring NBR | | | |
| 53001010 | PG 7 | 10.0 x 1.5 | 100 |
| 53102011 | PG 9 | 13.0 x 1.5 | 100 |
| 53001020 | PG 11 | 16.0 x 1.5 | 100 |
| 52005740 | PG 13,5 | 18.0 x 1.5 | 100 |
| 53001030 | PG 16 | 20.0 x 1.5 | 100 |
| 52005750 | PG 21 | 26.0 x 2.0 | 100 |
| 53001040 | PG 29 | 34.0 x 2.0 | 50 |
| 52005760 | PG 36 | 44.0 x 2.0 | 50 |
| 53001050 | PG 42 | 50.0 x 2.0 | 50 |
| 52005770 | PG 48 | 55.0 x 2.0 | 50 |

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16