

SKINDICHT® RWV-M without E+D

SKINDICHT® RWV-M without E+D, angle cable gland with cable running parallel to the housing wall, corrosion-resistant and combinable



Corrosion-resistant



Space requirement



Connector with standard housing unit



Temperature-resistant

Benefits

- Combination of different conduit glands is possible
- Space- and weight-saving application due to thin cable diameters
- Decrease in installation height
- Cable runs parallel to the housing wall
- Corrosion-resistant

Application range

- Angled glands are used in areas where cables have to run in parallel to the housing wall.
- Electric motor manufacturing
- Machine and equipment manufacturing
- Plant engineering
- Light and sound applications

Product Make-up

- Metric connection thread acc. to DIN EN 60423
- Basis for technical information DIN IEC 62444

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® RWV-M without E+D

Note

The protection class is dependent on the combination with the various special glands. The minimum standard is IP 55.

Counter nut to be used: SKINDICHT® SM-M

For combination with other SKINDICHT® or SKINTOP® cable glands, we propose our SKINDICHT® RWV-M without incised sealing ring (E) and compression screw (D)

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000441 ETIM 6.0 Class-Description: Cable screw gland
Material:	Body: zinc die-casting Hexagon nut: nickel-plated brass O-ring: NBR
Protection rating:	IP 55
Temperature range:	-20°C to +100°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® RWV-M without E+D

Article number	Article designation / size	B in mm	Thread length D mm	K	L	Ø G	SW1	Ø A1	SW2	Ø A2	Pieces / PU
SKINDICHT® RWV-M without E+D											
52107801	M 12 x 1,5	21	11.5	5	20.5	8	14.0	16	17.0	18.9	25
52107811	M 16 x 1,5	23	11.5	5	23.5	12	18.0	20	22.0	24.5	25
52107821	M 20 x 1,5	28.5	12.5	5	28.5	15	22.0	24	27.0	30.1	25
52107831	M 25 x 1,5	30	13.5	5	31	20	27.0	29	32.0	35.7	10
52107841	M 32 x 1,5	36.5	13.5	5	33.5	27	34.0	33.5	41.0	45.6	10
52107851	M 40 x 1,5	43	15.5	5	43	35	42.0	43	46.0	50.6	5