

SKINTOP® GMP-HF-M

SKINTOP® GMP-HF-M, halogen-free counter nuts, extremely flame-retardant, self-extinguishing, no dripping, for public buildings



Halogen-free



Assembly time



Temperature-resistant



Variety of approval certifications

Benefits

Halogen-free

Extremely flame-retardant according to UL 94 V0

Self-extinguishing, no dripping

Application range

Airports

Tunnel construction

Underground railways

Public buildings

Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

Note

Designed for use with SKINTOP® ST-HF-M

SKINTOP® GMP-HF-M

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000940 ETIM 5.0 Class-Description: Locknut for cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000940 ETIM 6.0 Class-Description: Locknut for cable screw gland
Colour delivered:	Light grey (RAL 7035) Black (RAL 9005), UV-resistant
Material:	halogenfree polyamide acc. to UL 94 V0
Temperature range:	Fixed: -40 °C to +100 °C Dynamic: -20 °C to +100 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINTOP® GMP-HF-M

Article number	Article designation / size	SW wrench size mm	PU
SKINTOP® GMP-HF-M light grey			
53119200	M 12 x 1,5	17	100
53119210	M 16 x 1,5	22	100
53119220	M 20 x 1,5	27	100
53119230	M 25 x 1,5	34	100
53119240	M 32 x 1,5	41	100
53119250	M 40 x 1,5	50	25
53119260	M 50 x 1,5	60	25
53119270	M 63 x 1,5	75	25
53119235	M 25 x 1,5	34	100

Last Update (11.07.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16