


SKINTOP® DIX-DV

SKINTOP® DIX-DV, metric multiple sealing inserts, prevents water and dust penetrating into unused bore holes



Assembly time



Optimum strain relief

Benefits

Prevents water and dust penetrating into unused bore holes of SKINTOP® DIX-M multiple sealing inserts

Application range

For inserting into unoccupied holes of the SKINTOP® DIX-M multiple sealing inserts, to ensure protection class

Note

When assembled professionally and properly, the protection class of IP 68 can be reached

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000032 ETIM 5.0 Class-Description: Plug for cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000032 ETIM 6.0 Class-Description: Plug for cable screw gland
Colour delivered:	Natural
Material:	Polyamide
Protection rating:	IP 54
Temperature range:	-30 °C to +100 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINTOP® DIX-DV

Article number	Article designation / size	PL_DYN_DURCHMESSER	Height (mm)	Pieces / PU
SKINTOP® DIX-DV				
53100003	DIX-DV 3 x 9	3.0	9.0	100
53100004	DIX-DV 4 x 9	4.0	9.0	100
53100005	DIX-DV 5 x 11	5.0	11.0	100
53100055	DIX-DV 5,5 x 11	5.5	11.0	100
53100006	DIX-DV 6 x 14	6.0	14.0	100
53100007	DIX-DV 7 x 14	7.0	14.0	100
53100008	DIX-DV 8 x 14	8.0	14.0	100
53100009	DIX-DV 9 x 14	9.0	14.0	100

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16