

# SKINTOP® SDVR-M ATEX

SKINTOP® SDV-M ATEX Dust protection



Assembly time



Reliability

## Benefits

Permanent and secure sealing for areas with risks of explosion  
Easy to assemble  
High degree of protection

## Application range

SKINTOP® SDVR-M is used together with SKINTOP® MSR-M ATEX or SKINTOP® KR-M ATEX plus (blue)  
Equipment group II / Category 2G+1D

## Note

Outside areas with a risk of explosion, also suitable for use in combination with SKINTOP® STR-M and SKINTOP® MSR-M

## Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000032

ETIM 5.0 Class-Description: Plug for cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000032

ETIM 6.0 Class-Description: Plug for cable screw gland

Caution:

Refer to the instruction leaflet for the installation dimensions and torques

Material:

CR

Protection rating:

IP 68 - 10 bar

Temperature range:

-30 °C to +70 °C

Short-term: up to +90 °C

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SKINTOP® SDVR-M ATEX

**Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINTOP® SDVR-M ATEX**

Article number	Article designation / size	Visible height (mm)	PU
SKINTOP® SDVR-M ATEX			
54113013	M 16 ATEX	4.0	50
54113023	M 20 ATEX	5.0	50
54113033	M 25 ATEX	5.0	50
54113043	M 32 ATEX	5.5	25