


SKINTOP® FIBER

SKINTOP® FIBER, cable gland for fiber optic cables, strain relief and sealing

Info

Enables a good fixation and sealing without impairing the transmission performance



Assembly time

Benefits

- Special sealing insert with 12 x 0-3mm clamping range
- Easy assembly and disassembly thanks to the insertion aid
- Smooth clamping of sensitive fibre optic cables due to the soft EPDM material
- The slotted holes allow the insertion of pre-assembled fiber optical cables

Application range

- Assembly of fiber optic cables
- Broadband expansion
- FTTx applications
- Industry 4.0 applications
- Suitable for indoor and outdoor use

Product Make-up

- Metric connection thread acc. to DIN EN 60423
- Basis for technical information DIN IEC 62444

Note

To achieve a high degree of protection, unoccupied holes can be closed with a SKINTOP DIX-DV plug

Included

Counter nut SKINTOP® GMP-GL-M included

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® FIBER

Technical Data

Caution:	Tightening torques see installation instructions
Colour delivered:	RAL 7035 light grey
Material:	Body: Polyamide Seal: EPDM (uv- and ozone-resistant)
Protection rating:	IP 66 (at maximum use of all boreholes)
Temperature range:	-20°C to +100°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.



SKINTOP® FIBER

Article number	Article designation / size	Ø F mm	SW wrench size mm	Overall length C mm	Thread length D mm	Pieces / PU
54113180	M 32 x 1,5	0 - 3	36	47.0	10	10

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® FIBER

