

SKINTOP® STR-M

SKINTOP® STR-M, increased oil-resistant plastic cable gland with permanent vibration protection and reducing seal insert

Info

With IP69 approval! Proven to withstand the most demanding cleaning procedures for industrial machinery with high-pressure cleaners and hot water!



-  Wide clamping range
-  Maximum vibration protection
-  Mechanical resistance
-  Assembly time
-  Optimum strain relief
-  Temperature-resistant
-  Variety of approval certifications

Benefits

High oil-resistance for maximum reliability
 Permanent vibration protection
 Wide, variable clamping ranges
 Optimum strain relief
 Various accessories (e.g. multiple sealing inserts)

Last Update (22.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® STR-M

Application range

With reducing seal insert, to seal cables with smaller outer diameters

Norm references / Approvals

UL File Nr. E79903

GGVS: TÜ.EGG.020-95

Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

Note

SKINTOP® ST(R) M ISO types have an extra-long connection thread

SKINTOP® ST(R) M ISO versions with extra-long connection thread, see table, no DNV approval

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000441 ETIM 6.0 Class-Description: Cable screw gland
Caution:	Refer to Appendix T21 for the installation dimensions and torques Size M 40 x 1,5 up tp M 63 x 1,5 with O-ring
Colour delivered:	Silver grey (RAL 7001) Light grey (RAL 7035) Black (RAL 9005), UV-resistant
Material:	Body: Polyamide Seal: CR
Tests:	GGVS: TÜ.EGG.020-95
Protection rating:	IP 66 IP 68 - 5 bar IP 69 NEMA Type 1, 12
Temperature range:	Fixed: -40 °C to +100 °C Dynamic: -20 °C to +100 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINTOP® STR-M

Article number	Article designation / size	Ø F mm	SW wrench size mm	Overall length C mm	Thread length D mm	Pieces / PU
SKINTOP® STR-M silver grey						
53111100	M 12 x 1,5	2 - 5	15	30.0	8	100
53111110	M 16 x 1,5	3.5 - 7	19	34.0	8	100
53111120	M 20 x 1,5	4 - 10	25	37.0	9	100
53111130	M 25 x 1,5	5 - 13	30	40.0	10	50
53111140	M 32 x 1,5	6 - 15	36	47.0	10	25
53111150	M 40 x 1,5	9 - 23	46	52.0	10	10
53111160	M 50 x 1,5	24 - 29	55	62.0	12	5
53111170	M 63 x 1,5	28 - 39	66	71.0	12	5
SKINTOP® STR-M black						
53111300	M 12 x 1,5	2 - 5	15	30.0	8	100
53111310	M 16 x 1,5	3.5 - 7	19	34.0	8	100
53111320	M 20 x 1,5	4 - 10	25	37.0	9	100
53111330	M 25 x 1,5	5 - 13	30	40.0	10	50
53111340	M 32 x 1,5	6 - 15	36	47.0	10	25
53111350	M 40 x 1,5	9 - 23	46	52.0	10	10
53111360	M 50 x 1,5	24 - 29	55	62.0	12	5
53111370	M 63 x 1,5	28 - 39	66	71.0	12	5
SKINTOP® STR-M light grey						
53111500	M 12 x 1,5	2 - 5	15	30.0	8	100
53111510	M 16 x 1,5	3.5 - 7	19	34.0	8	100
53111520	M 20 x 1,5	4 - 10	25	37.0	9	100
53111530	M 25 x 1,5	5 - 13	30	40.0	10	50
53111540	M 32 x 1,5	6 - 15	36	47.0	10	25
53111550	M 40 x 1,5	9 - 23	46	52.0	10	10
53111560	M 50 x 1,5	24 - 29	55	62.0	12	5
53111570	M 63 x 1,5	28 - 39	66	71.0	12	5
SKINTOP® STR M ISO silver-grey (with long metric connecting thread)						
53017110	M 16 x 1,5 ISO	2 - 6	19	40.0	12	100
53017130	M 20 x 1,5 ISO	4 - 9	24	45.0	13	100
53017140	M 25 x 1,5 ISO	6 - 12	27	47.0	13	50
SKINTOP® STR M ISO black (with long metric connecting thread)						
53017310	M 16 x 1,5 ISO	2 - 6	19	40.0	12	100
53017330	M 20 x 1,5 ISO	4 - 9	24	45.0	13	100
53017340	M 25 x 1,5 ISO	6 - 12	27	47.0	13	50

Last Update (22.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® STR-M

