


SKINTOP® INOX SC

SKINTOP® INOX EMC corrosion-resistant stainless steel cable gland with smooth surfaces, compact design, sea water-resistant

Info

Stainless steel version with compact design
Optimum EMC protection



-  Food & Beverage
-  Suitable for outdoor use
-  Good chemical resistance
-  Wide clamping range
-  Halogen-free
-  Mechanical resistance
-  Interference signals
-  Temperature-resistant

Benefits

Smooth surfaces - no edges
Compact design
Wide, variable clamping ranges

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® INOX SC

Low-resistance screen contact, optimum EMC protection
Highly conductive, flexible EMC contact for clamping various screen diameters

Application range

For EMC-compliant earthing of the copper braiding
Pharmaceutical industry
Food industry (product-free zone, splash zone)
Onshore and offshore applications
Bottling plants and breweries

Norm references / Approvals

DIN EN ISO 14159
Security of machinery – Hygienic requirements for the design of machinery
DIN EN 1672-2
Guideline for the design of machinery
ECOLAB®
Industry standard in the field of professional cleaning and disinfection in the food and beverage industry
NSF/ANSI 169
Hygienic design for machinery and components

Product Make-up

Metric connection thread acc. to DIN EN 60423
Basis for technical information DIN IEC 62444

Note

SKINDICHT® SM-PE-M counter nut should be used to ensure optimum contact with painted, anodised or powder-coated housings

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000441 ETIM 6.0 Class-Description: Cable screw gland
Caution:	Refer to the instruction leaflet for the installation dimensions and torques
Material:	Body: stainless steel V4A (1.4404 / 316L) Insert: polyamide Sealing: silicone O-Ring: silicone Halogen-free
Protection rating:	IP 68 - 10 bar (M12 - M20) IP 68 - 5 bar (M25 - M50) IP 69 NEMA Type 1, 2, 4x, 6, 12
Temperature range:	-40°C to +100°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® INOX SC

Article number	Article designation / size	Ø F mm	SW wrench size mm	Overall length C mm	Thread length D mm	Pieces / PU
SKINTOP® INOX SC						
53806720	M 12 x 1,5	4 - 7	16	29.3	6.5	5
53806722	M 16 x 1,5	6 - 10	20	32.4	7	5
53806724	M 20 x 1,5	7 - 13	24	35.5	8	5
53806726	M 25 x 1,5	9 - 17	29	39.2	8	5
53806728	M 32 x 1,5	11 - 21	36	44.6	9	5
53806731	M 40 x 1,5	19 - 28	45	51.2	9	5

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16