

EPIC® DATA CCR FA

Cable coupler round

Field mountable round cable coupler, IP67, IDC, qualified for 10 Gigabit

Info

installation without tools



Supplementary automation components from Lapp



Mechanical and plant engineering



Wide clamping range



Mechanical resistance



Space requirement



Interference signals

Product features

field mountable cable coupler for data cables up to Cat.7A

compact, round design

Qualified for 10 Gigabit/s Ethernet

Suitable for use in industrial applications

Robust and vibrations- resistant

Housing: zinc die-casting, grey

Norm references / Approvals

compliance to class FA up to 1000 MHz in connection with Cat.7A cables

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® DATA CCR FA

Cat.7_A acc. to ISO/IEC 11801

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001121

ETIM 5.0 Class-Description: Modular connector

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001121

ETIM 6.0 Class-Description: Modular connector

Protection rating:

IP 67

Ambient temperature (operation):

Plug/socket -40°C to +85°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® DATA CCR FA

Article number	Article designation	Min. outer diameter (mm)	Max. outer diameter (mm)	Max. core diameter including insulation	AWG solid	AWG 7-wire
21700623	EPIC® DATA CCR FA	5	9.7	1.6	26 - 22	26 - 22