


Connector RJ45 CAT.5 Stewart SS37

RJ45 field mountable connector, qualified for 100Mbit - data transmission
suitable for industrial environment and Officearea
Stewart SS37



Product features

Screened version
Suitable for stranded conductors (AWG26)
Included: bend protection and guide plate
Anti-kink protection: light grey
Max. outer sheath diameter: 5.72 mm

Technical Data

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002641

ETIM 6.0 Class-Description: Modular connector (industrial connector)

Note

Stewart is a registered trademark of Bel Fuse Inc.

Other colours are available upon request.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Connector RJ45 CAT.5 Stewart SS37

Article number	Article designation
CE6323	Connector RJ45 CAT.5 Stewart SS37