

EPIC® SENSOR M8

Field mountable connectors M8

Field mountable M8 connectors with screw connection or fast-connect versions for connection of sensors and actuators with individual cable lengths



Mechanical and plant engineering



Wide clamping range



Assembly time



Space requirement



Robust



Waterproof

Benefits

Easy connection with proven screw clamp connection
For creating of individual cable lengths
Quick and easy on-site assembly
No special tools required for connecting the cables
Time-saving assembly with IDC connection technology

Product features

3 and 4-pin version
Version with piercing, insulation displacement contacts (IDC) or screw connection
PWIS-free

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002062

ETIM 5.0 Class-Description: Sensor-actuator connector

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® SENSOR M8

Classification ETIM 6:	ETIM 6.0 Class-ID: EC002062 ETIM 6.0 Class-Description: Sensor-actuator connector
Material:	Contact: CuZn Contact surface: Au (gold)
Protection rating:	IP 65/IP 67 (IDC) IP 68 (piercing) IP 67 (screw)
Ambient temperature (operation):	Plug/socket -25 °C to +80 °C (IDC) -25 °C to +85 °C (piercing) -40 °C to +85 °C (screw)
Coding:	A-standard
Rated current (A):	4 A

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® SENSOR M8

Article number	Article designation	Number of pins	Connection type	Cross-section in mm²	Cable diameter in mm	Rated voltage (V)	PU
Plug, straight							
22260993	AB-C3-M8MS-F0,25	3	IDC	0.08 - 0.25	2.5 - 5	60	1
22260985	AB-C3-M8MS-F0,5	3	IDC	0.25 - 0.5	2.5 - 5	60	1
22260043	AB-C4-M8MS-F0,25	4	IDC	0.08 - 0.25	2.5 - 5	60	1
22260044	AB-C4-M8MS-F0,5	4	IDC	0.25 - 0.5	2.5 - 5	60	1
22260120	AB-C3-M8MS	3	screw	0.14 - 0.5	3.5 - 5	60	1
22260121	AB-C4-M8MS	4	screw	0.14 - 0.5	3.5 - 5	60	1
Plug, straight shielded							
22262025	AB-C3-M8MS-M-0,34-SH	3	screw	0.14 - 0.5	3.5 - 5.5	60	1
22262027	AB-C4-M8MS-M-0,34-SH	4	screw	0.14 - 0.5	3.5 - 5	60	1
Plug, angled							
22262110	AB-C3-M8MA	3	screw	0.14 - 0.5	3.5 - 5	60	1
22262111	AB-C4-M8MA	4	screw	0.14 - 0.5	3.5 - 5	60	1
Socket, straight							
22260994	AB-C3-M8FS-F0,25	3	IDC	0.08 - 0.25	2.5 - 5	60	1
22260986	AB-C3-M8FS-F0,5	3	IDC	0.25 - 0.5	2.5 - 5	60	1
22260045	AB-C4-M8FS-F0,25	4	IDC	0.08 - 0.25	2.5 - 5	60	1
22260046	AB-C4-M8FS-F0,5	4	IDC	0.25 - 0.5	2.5 - 5	60	1
22260125	AB-C3-M8FS	3	screw	0.14 - 0.5	3.5 - 5	60	1
22260126	AB-C4-M8FS	4	screw	0.14 - 0.5	3.5 - 5	60	1
Socket, straight shielded							
22262026	AB-C3-M8FS-M-0,34-SH	3	screw	0.14 - 0.5	3.5 - 5.5	60	1
22262028	AB-C4-M8FS-M-0,34-SH	4	screw	0.14 - 0.5	3.5 - 5.5	60	1
Socket, angled							
22262112	AB-C3-M8FA	3	screw	0.14 - 0.5	3.5 - 5	60	1
22262113	AB-C4-M8FA	4	screw	0.14 - 0.5	3.5 - 5	60	1