


UNITRONIC® SENSOR M12Y

M12 Y plug straight on 2x free conductor end

Sensor/Actuator-cable, Y-connector 3-pole, straight Y-M12-plug on 2 free conductor endings, A-coded, PUR LSZH, suitable for drag chains



Supplementary automation components from Lapp



Mechanical and plant engineering



Space requirement



Power chain



Waterproof

Benefits

Cost-saving due to quick and easy installation

Space-saving due to compact dimensions.

Product features

4-pin M12Y plug on

free conductor end

Including tag carrier

PWIS-free

Suitable for drag chains

Product Make-up

3 x 0.34 mm²

Core colours: bn, bu, bk

Outer sheath: PUR halogen-free, black

Last Update (12.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

UNITRONIC® SENSOR M12Y

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001855 ETIM 5.0 Class-Description: Sensor-actuator patch cord
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001855 ETIM 6.0 Class-Description: Sensor-actuator patch cord
Material:	Contact: CuSn Contact surface: Ni/Au Knurl: Zinc die-cast, nickel-plated Gripping body: TPU, flame-retardant, self-extinguishing
Protection rating:	IP65/IP67/IP68
Ambient temperature (operation):	Plug/socket -25°C to +90°C Fixed installation -40°C to +80°C Flexing -25°C to +80°C
Coding:	A-standard
Rated current (A):	4 A

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: inclusive of copper. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

UL certifications can be found in the data sheet.

UNITRONIC® SENSOR M12Y

Article number	Article designation	Length (m)	LED	Rated voltage (V)	PU
Y plug to 2 x free conductor end					
22260500	AB-C3-M12Y-2,0PUR	2	no	250	1
22260513	AB-C3-M12Y-5,0PUR	5	no	250	1
22260526	AB-C3-M12Y-10,0PUR	10	no	250	1