

EPIC® M12L/K Contacts

Contacts with multiple slots and conductor cross-section marking, for EPIC® POWER M12L and M12K power connectors.

Not all contacts are the same! To make sure that the miniaturised power connector EPIC® POWER M12L and M12K to do its job properly, long-lasting contacts are required that make maximum contact at the connector and keep contact resistances low. Et voilà, here they are!

Info

Made in Germany



Benefits

With improved contacting due to multiple slots.
Clear marking of the maximum conductor cross-section prevents incorrect assembly.
With corrosion-resistant gold coating for low contact resistance and long product life.
Suitable for conductor cross-sections up to 2.5 mm².

Application range

For use with EPIC® POWER M12L and M12K circular connectors.

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000796 ETIM 5.0 Class-Description: Contact for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000796 ETIM 6.0 Class-Description: Contact for industrial connectors
Termination methods:	0.75mm ² - 2.5mm ²
Material:	brass gold plated CuZn / Au

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® M12L/K Contacts

Article number	Article description	Pieces / PU
44423189	-	100
44423186	-	100
44423191	-	100
44423188	-	100
44423412	Solder termination	100
44423414	Solder termination	100

Last Update (31.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® M12L/K Contacts

