

EPIC® SIGNAL M23 Contacts male

Contacts, tools, accessories for circular connectors M23

EPIC® SIGNAL M23 Contacts male for M23 circular connector series

Info

All contacts are high quality gold plated

Contacts are designed for wide crimping range, therefore low number of variants

Made in Germany



Good chemical resistance



Corrosion-resistant



Mechanical resistance



Oil-resistant



Optimum strain relief



Robust



Reliability

Technical Data

Classification ETIM 6:

ETIM 6.0 Class-Description: Contact for industrial connectors

Material:

brass gold plated CuZn / Au

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (23.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® SIGNAL M23 Contacts male

Article number	Article designation	Version	For design	Pieces / PU
1mm contacts, male				
72400001	-	1 mm male 0.14 - 1.0 mm ²	M23 inserts (not D-Sub)	10
72400000	-	1 mm male 0.14 - 1.0 mm ²	M23 inserts (not D-Sub)	100
72402001	-	1 mm male solder	M23 inserts (not D-Sub)	10
72402000	-	1 mm male solder	M23 inserts (not D-Sub)	100
2mm contacts, male				
72401000	-	2 mm male crimp	M23 inserts (not D-Sub)	100
72403100	-	2 mm male solder	M23 inserts (not D-Sub)	10
72403000	-	2 mm male solder	M23 inserts (not D-Sub)	100

EPIC® SIGNAL M23 Contacts male