

EPIC® H-D 1.6 stamped contacts-on-reel

For inserts and modules of the EPIC® rectangular connectors

The pressed contacts in ring are offered in variable variants for various conductor cross-sections and length of stripped insulation.

Info

Choice of high quality gold or silver plated contacts
for automated production with crimping machine
Two crimp areas with wire and insulation crimp



Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 Class-Description: Contact for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-D 1.6 stamped contacts-on-reel

Article number	Article description	Contact type	Conductor cross-section (mm²)	Surface	Stripping length (mm)	Note	Pieces / PU
Contacts							
11240700	H-D SCBG AG 0.14-0.5 200 LI	male	0.14 - 0.5	Ag	3,0	1 reel (PU) = 200 contacts	1
11230700	H-D BCBG AG 0.14-0.5 200 LI	female	0.14 - 0.5	Ag	3,0	1 reel (PU) = 200 contacts	1
11240400	H-D SCBG AG 0.14-0.5 2000 LI	male	0.14 - 0.5	Ag	3,0	1 reel (PU) = 2000 contacts	1
11230400	H-D BCBG AG 0.14-0.5 2000 LI	female	0.14 - 0.5	Ag	3,0	1 reel (PU) = 2000 contacts	1
11240000	H-D SCBG AG 0.14-0.5 2000 RE	male	0.14 - 0.5	Ag	3,0	1 reel (PU) = 2000 contacts	1
11230000	H-D BCBG AG 0.14-0.5 2000 RE	female	0.14 - 0.5	Ag	3,0	1 reel (PU) = 2000 contacts	1
11240500	H-D SCBG AU 0.14-0.5 2000 LI	male	0.14 - 0.5	Au	3,0	1 reel (PU) = 2000 contacts	1
11230500	H-D BCBG AU 0.14-0.5 2000 LI	female	0.14 - 0.5	Au	3,0	1 reel (PU) = 2000 contacts	1
11220700	H-D SCBG AG 0.5-1.5 200 LI	male	0.5 - 1.5	Ag	4,0	1 reel (PU) = 200 contacts	1
11235700	H-D BCBG AG 0.14-0.5 200 LI	female	0.5 - 1.5	Ag	4,0	1 reel (PU) = 200 contacts	1
11226000	H-D SCBG AG 0.5-1.5 2000 LI	male	0.5 - 1.5	Ag	4,0	1 reel (PU) = 2000 contacts	1
11226500	H-D BCBG AG 0.5-1.5 2000 LI	female	0.5 - 1.5	Ag	4,0	1 reel (PU) = 2000 contacts	1
11220000	H-D SCBG AG 0.5-1.5 2000 RE	male	0.5 - 1.5	Ag	4,0	1 reel (PU) = 2000 contacts	1
11235000	H-D BCBG AG 0.5-1.5 2000 RE	female	0.5 - 1.5	Ag	4,0	1 reel (PU) = 2000 contacts	1
11220100	H-D SCBG AU 0.5-1.5 2000 RE	male	0.5 - 1.5	Au	4,0	1 reel (PU) = 2000 contacts	1
11235200	H-D BCBG AG 0.5-1.5 200 LI	female	0.5 - 1.5	Au	4,0	1 reel (PU) = 2000 contacts	1
11223000	H-D SCBG AG 1.5-2.5 100 LI	male	1.5 - 2.5	Ag	4,0	1 reel (PU) = 100 contacts	1
11228000	H-D BCBG AG 1.5-2.5 100 LI	female	1.5 - 2.5	Ag	4,0	1 reel (PU) = 100 contacts	1
11222700	H-D SCBG AG 1.5-2.5 2000 LI	male	1.5 - 2.5	Ag	4,0	1 reel (PU) = 2000 contacts	1

EPIC® H-D 1.6 stamped contacts-on-reel

Article number	Article description	Contact type	Conductor cross-section (mm²)	Surface	Stripping length (mm)	Note	Pieces / PU
11227700	H-D BCBG AG 1.5-2.5 2000 LI	female	1.5 - 2.5	Ag	4,0	1 reel (PU) = 2000 contacts	1

EPIC® H-D 1.6 stamped contacts-on-reel