


EPIC® H-B 16 TG 2X

Housing design H-B. The industry standard.

The universal robust low housing consists of pivots for a single lever and 2 direct cable entries and is suitable for investment construction.

Info

Non-slip ridges for comfortable disconnecting
For easy introduction of two cables
Protection rating UL50E tested



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

The housing standard. Wide choice for all applications

Application range

Plant engineering
Light & sound technology
Plastics industry

Last Update (24.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 16 TG 2X

Product features

Hood, low version
Bolts for double lever
2 straight cable entries
Versions with neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 16 TG 2X

Article number	Article description	M	Neck	Pieces / PU
H-B housing: hood (2 straight cable entries, bolts for double lever)				
19080500	H-B 16 TG 2XM25	2 x 25	yes	5