



EPIC® H-B 24 SDRLH-BO

Housing design H-B. The industry standard.

The housing for installation in rectangular connectors has 2 cable entries and pivots for a double lever. It can be used, for example, in investment construction.

Info

For easy introduction of two cables
Metal lid with sturdy hinge
Protection rating UL50E tested



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

Safe fixing with 4 screws
Casted neck for easy assembly of the cable gland
More interior space for wiring

Application range

Plant engineering
Light & sound technology
Plastics industry

Last Update (16.07.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 24 SDRLH-BO

Product features

Surface-mount base, high version
Bolts for double lever
2 cable entries
Metal cover

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) IP 40 (cover closed) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40°C to +100°C, short-term up to +125°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 24 SDRLH-BO

Article number	Article description	M	PG	Packaging unit
H-B housing: surface-mount base (cover, 2 cable entries, bolts for double lever, high version)				
70146200	H-B 24 SDRLH-BO 21	-	21	5
70146400	H-B 24 SDRLH-BO 29	-	29	5
79146400	H-B 24 SDRLH-BO M32	32	-	5