

EPIC® H-B 24 TGH 2X

Housing design H-B. The industry standard.


The robust universal housing with pivots for a direct lever and 2 cable entries is the perfect choice for use in investment construction.

Info

Non-slip ridges for comfortable disconnecting

For easy introduction of two cables

Protection rating UL50E tested



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

Ideal for many applications due to a wide range of housings and inserts

More interior space for wiring

Application range

Plant engineering

Light & sound technology

Plastics industry

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 24 TGH 2X

Product features

Hood, high version
Bolts for double lever
2 straight cable entries
Versions without neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 24 TGH 2X

Article number	Article description	M	Pieces / PU
H-B housing: hood (2 straight cable entries, bolts for double lever, high version)			
44422021	H-B 24 TGH 2XM25	2 x 25	5
79178500	H-B 24 TGH 2XM32	2 x 32	5