

## EPIC® H-B 24 TS


Housing design H-B. The industry standard.

The robust connector housing can withstand temperatures of up to +125 degrees for a short period and is suitable for use in the plastics industry.

### Info

Non-slip ridges for comfortable disconnecting

Protection rating UL50E tested



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

### Benefits

Ideal for many applications due to a wide range of housings and inserts

### Application range

Plant engineering

Light & sound technology

Plastics industry

### Product features

Last Update (16.07.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® H-B 24 TS

Hood, low version  
Bolts for double lever  
Side cable entry  
Versions with neck

### Technical Data

|                        |                                                                                              |
|------------------------|----------------------------------------------------------------------------------------------|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000437<br>ETIM 5.0 Class-Description: Housing for industrial connectors |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000437<br>ETIM 6.0 Class-Description: Housing for industrial connectors |
| Material:              | Housing: powder-coated aluminium alloy, grey<br>Lever: zinc-plated steel<br>Sealing: NBR     |
| Protection rating:     | IP 65 (latched)<br>NEMA 250, UL50E: 12, 4 (latched)                                          |
| VDE-tested:            | Certified production control: VDE-REG. no.: B437<br>UL-tested:<br>UL File Number: E75770     |
| Temperature range:     | -40°C to +100°C, short-term up to +125°C                                                     |

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® H-B 24 TS**

| Article number                                               | Article description | M  | PG | Neck | Packaging unit |
|--------------------------------------------------------------|---------------------|----|----|------|----------------|
| H-B housing: hood (side cable entry, bolts for double lever) |                     |    |    |      |                |
| 10113000                                                     | H-B 24 TS 21        | -  | 21 | yes  | 5              |
| 10123000                                                     | H-B 24 TS 29        | -  | 29 | yes  | 5              |
| 19113000                                                     | H-B 24 TS M25       | 25 | -  | yes  | 5              |
| 19123000                                                     | H-B 24 TS M32       | 32 | -  | yes  | 5              |