


EPIC® H-B 48 SDR-LB

Housing design H-B for 2 inserts.

The large housing for the placement of two inserts consists of a single lever, a cable entry and a thermoplastic cap.



Benefits

The large, robust housing for two inserts in one connector. Power and data in a single connector
M40 housing extension on M50 with SKINTOP 53112083 possible (clamping range 27 - 35 mm)

Application range

Plant engineering
Plastics industry

Product features

Surface-mount base
Single lever
1 cable entry
Plastic cover

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000437

ETIM 5.0 Class-Description: Housing for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000437

ETIM 6.0 Class-Description: Housing for industrial connectors

Material:

Housing: powder-coated aluminium alloy, grey

Lever: zinc-plated steel

Sealing: NBR

Protection rating:

IP 65 (latched)

Temperature range:

-40°C to +100°C, short-term up to +125°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Last Update (22.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 48 SDR-LB

Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 48 SDR-LB

Article number	Article description	M	PG	Pieces / PU
H-B housing: surface-mount base (cover, 1 cable entry, single lever)				
10167000	H-B 48 SDR 29	-	29	1
10167100	H-B 48 SDR 36	-	36	1
19167000	H-B 48 SDR M32	32	-	1
19167100	H-B 48 SDR M40	40	-	1