


EPIC® H-B 48 TG

Housing design H-B for 2 inserts.

The robust large housing for two inserts in one connector ensures that the power and data are in a single component. It is suitable, for example, for use in the plastics industry.



Benefits

The large, robust housing for two inserts in one connector. Power and data in a single connector

Application range

Plant engineering
Plastics industry

Product features

Hood
Bolts for single lever
Straight cable entry
Versions with / without neck

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000437

ETIM 5.0 Class-Description: Housing for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000437

ETIM 6.0 Class-Description: Housing for industrial connectors

Material:

Housing: aluminium alloy, grey

Lever: zinc-plated steel

Sealing: NBR

Protection rating:

IP 65 (latched)

Temperature range:

-40°C to +100°C, short-term up to +125°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 48 TG

Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 48 TG

Article number	Article description	M	PG	Neck	Pieces / PU
H-B housing: hood (straight cable entry, bolts for single lever)					
10155000	H-B 48 TG 29	-	29	yes	1
10156000	H-B 48 TG 36	-	36	yes	1
10156200	H-B 48 TG 36	-	36	-	1
10157000	H-B 48 TG 42	-	42	yes	1
19155000	H-B 48 TG M32	32	-	-	1
19156000	H-B 48 TG M40	40	-	-	1
19157000	H-B 48 TG M50	50	-	-	1