

EPIC® H-Q 7 PE-Screw termination

Connector insert with 7 crimping contacts and protection earth screwing contact

Compact, 7-pole rectangular connector insert, powerful up to 10 A, with screwable PE contact.

Info

Compact, powerful standard insert

Space saving, crimping contact

Made in Germany



Supplementary automation components from Lapp



Food & Beverage



Mechanical and plant engineering



Rail



Wind Energy



Suitable for outdoor use



Flame-retardant

Benefits

Compact contact arrangement allows 7 contacts + 1 PE contact in a small installation space.

Crimp connection creates a vibration-proof connection, ensures maximum contacting reliability between contact and cable and is suitable for automated assembly.

Last Update (13.07.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-Q 7 PE-Screw termination

Protective earth (PE) can be connected in two ways: Variant "PE-S" can be used with a PE screw contact, variant "PE-C" with a PE crimp contact.

Mateable with market standard connectors.

Suitable for conductor cross-sections from 0.14 - 2.50 mm².

Application range

For power supply connection of devices and machines in various applications.

Suitable for wiring inside the control cabinet.

Can be used with many EPIC® rectangular connector housings.

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000438 ETIM 5.0 Class-Description: Contact insert for industrial connectors
Classification ETIM 6:	ETIM 5.0 Class-ID: EC000438 ETIM 6.0 Class-Description: Contact insert for industrial connectors
Rated voltage (V):	400 V
Rated impulse voltage:	6 kV
Rated current (A):	10 A
Pollution degree:	3
Flammability:	UL94 V-0
Contact resistance:	< 2 mOhm
Number of contacts:	7 + PE
Termination methods:	Crimp termination: 0.14 - 2.5 mm ² Screw termination PE: 0.25 mm ² ... 4.0 mm ²
Material:	Polyamide
Cycle of mechanical operation:	500
VDE-tested:	UL-tested: UL File Number: E75770
Temperature range:	-40°C to +120°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-Q 7 PE-Screw termination

Article number	Article description	Contact type	Number of operating contacts	Packaging unit
EPIC® H-Q 7 with protectiv earth screw connection				
10431700	EPIC H-Q 7 SCM PE-S	male	7	10
10432700	EPIC H-Q 7 BCM PE-S	female	7	10

Last Update (13.07.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

EPIC® H-Q 7 PE-Screw termination

