

## FLEXIMARK® Character holders PGS

Pre-cutted FLEXIMARK® Character holders PGS for marking components in the electrical industry (as cabinets) with labels or character strips. For assembly with cable ties.

### Info

PGS 1-285 BK included in FLEXIMARK® sample bag (article no. M3251010)



Good chemical resistance



Flame-retardant



Halogen-free



Acid-resistant



UV-resistant

### Benefits

Self-adhesive on many surfaces

Transparent cover ensures an additional protection of the label or the character strips

### Application range

Suitable for FLEXIMARK® Flexilabels LFL as well as for DYMO® industry tapes

For marking component groups in the manufacturing of control cabinets

Fastening: bonding, or at temperatures > +45 °C with screws or rivets

### Product features

Extremely flame-retardant according to

UL 94 V0

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002248

ETIM 5.0 Class-Description: Mounting for labelling material

Last Update (22.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## FLEXIMARK® Character holders PGS

Classification ETIM 6:	ETIM 6.0 Class-ID: EC002248 ETIM 6.0 Class-Description: Mounting for labelling material
Colour delivered:	Black, white, grey
Material:	ABS plastic
Temperature range:	-20 °C to +45 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

**FLEXIMARK® Character holders PGS**

Article number	Article designation	Colour	Length x height (mm)	Markers / PU	PU
83252011	FLEXIMARK® PGS 10-1000 WH	white	1000.0 x 10.0	10	1
83250003	FLEXIMARK® PGS 10-1000 BK	black	1000.0 x 10.0	10	1
83252014	FLEXIMARK® PGS 10-1000 GY	grey	1000.0 x 10.0	10	1
83250043	FLEXIMARK® Label cover 10-100 PGS 10	transparent	1000.0 x 10.0	10	1