

ÖLFLEX® UNIPLUS TRI

ÖLFLEX® UNIPLUS TRI



Flame-retardant

Note

Unless otherwise specified, the product values shown are nominal values. You can receive further values, such as tolerances, upon request if they are available and have been released for publication.

Photographs are not to scale and do not represent detailed images of the respective products.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ÖLFLEX® UNIPLUS TRI

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Colour	Copper index (kg/km)	Weight (kg/km)
8201010100	1 X 0.5	2.6	black	4.8	11.7
8201010300	1 X 0.5	2.6	brown	4.8	11.7
8201010200	1 X 0.5	2.6	blue	4.8	11.7
8201011400	1 X 0.5	2.6	dark blue	4.8	11.7
8201011200	1 X 0.5	2.6	green	4.8	11.7
8201010600	1 X 0.5	2.6	grey	4.8	11.7
8201011500	1 X 0.5	2.6	light blue	4.8	11.7
8201010900	1 X 0.5	2.6	orange	4.8	11.7
8201010800	1 X 0.5	2.6	pink	4.8	11.7
8201010400	1 X 0.5	2.6	red	4.8	11.7
8201010700	1 X 0.5	2.6	violet	4.8	11.7
8201010500	1 X 0.5	2.6	white	4.8	11.7
8201011100	1 X 0.5	2.6	yellow	4.8	11.7
8201010000	1 X 0.5	2.6	green-yellow	4.8	11.7
8201010101	1 X 0.75	2.8	black	7.2	14.7
8201010301	1 X 0.75	2.8	brown	7.2	14.7
8201010201	1 X 0.75	2.8	blue	7.2	14.7
8201011401	1 X 0.75	2.8	dark blue	7.2	14.7
8201011201	1 X 0.75	2.8	green	7.2	14.7
8201010601	1 X 0.75	2.8	grey	7.2	14.7
8201011501	1 X 0.75	2.8	light blue	7.2	14.7
8201010901	1 X 0.75	2.8	orange	7.2	14.7
8201010801	1 X 0.75	2.8	pink	7.2	14.7
8201010401	1 X 0.75	2.8	red	7.2	14.7
8201010701	1 X 0.75	2.8	violet	7.2	14.7
8201010501	1 X 0.75	2.8	white	7.2	14.7
8201011101	1 X 0.75	2.8	yellow	7.2	14.7
8201010001	1 X 0.75	2.8	green-yellow	7.2	14.7
8201010102	1 X 1.0	3.0	black	9.6	17.6
8201010302	1 X 1.0	3.0	brown	9.6	17.6
8201010202	1 X 1.0	3.0	blue	9.6	17.6
8201011402	1 X 1.0	3.0	dark blue	9.6	17.6
8201011202	1 X 1.0	3.0	green	9.6	17.6
8201010602	1 X 1.0	3.0	grey	9.6	17.6

ÖLFLEX® UNIPLUS TRI

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Colour	Copper index (kg/km)	Weight (kg/km)
8201011502	1 X 1.0	3.0	light blue	9.6	17.6
8201010902	1 X 1.0	3.0	orange	9.6	17.6
8201010802	1 X 1.0	3.0	pink	9.6	17.6
8201010402	1 X 1.0	3.0	red	9.6	17.6
8201010702	1 X 1.0	3.0	violet	9.6	17.6
8201010502	1 X 1.0	3.0	white	9.6	17.6
8201011102	1 X 1.0	3.0	yellow	9.6	17.6
8201010002	1 X 1.0	3.0	yellow	9.6	17.6
8201010103	1 X 1.5	3.2	black	14.4	22.4
8201010303	1 X 1.5	3.2	brown	14.4	22.4
8201010203	1 X 1.5	3.2	blue	14.4	22.4
8201011403	1 X 1.5	3.2	dark blue	14.4	22.4
8201011203	1 X 1.5	3.2	green	14.4	22.4
8201010603	1 X 1.5	3.2	grey	14.4	22.4
8201011503	1 X 1.5	3.2	light blue	14.4	22.4
8201010903	1 X 1.5	3.2	orange	14.4	22.4
8201010803	1 X 1.5	3.2	pink	14.4	22.4
8201010403	1 X 1.5	3.2	red	14.4	22.4
8201010703	1 X 1.5	3.2	violet	14.4	22.4
8201010503	1 X 1.5	3.2	white	14.4	22.4
8201011103	1 X 1.5	3.2	yellow	14.4	22.4
8201010003	1 X 1.5	3.2	green-yellow	14.4	22.4
8201010104	1 X 2.5	3.7	black	24	32.7
8201010304	1 X 2.5	3.7	brown	24	32.7
8201010204	1 X 2.5	3.7	blue	24	32.7
8201011404	1 X 2.5	3.7	dark blue	24	32.7
8201011204	1 X 2.5	3.7	green	24	32.7
8201010604	1 X 2.5	3.7	grey	24	32.7
8201011504	1 X 2.5	3.7	light blue	24	32.7
8201010904	1 X 2.5	3.7	orange	24	32.7
8201010804	1 X 2.5	3.7	pink	24	32.7
8201010404	1 X 2.5	3.7	red	24	32.7
8201010704	1 X 2.5	3.7	violet	24	32.7
8201010504	1 X 2.5	3.7	white	24	32.7

ÖLFLEX® UNIPLUS TRI

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Colour	Copper index (kg/km)	Weight (kg/km)
8201011104	1 X 2.5	3.7	yellow	24	32.7
8201010004	1 X 2.5	3.7	green-yellow	24	32.7
8201010105	1 X 4.0	4.2	black	38.4	47
8201010305	1 X 4.0	4.2	brown	38.4	47
8201010205	1 X 4.0	4.2	blue	38.4	47
8201011405	1 X 4.0	4.2	dark blue	38.4	47
8201011205	1 X 4.0	4.2	green	38.4	47
8201010605	1 X 4.0	4.2	grey	38.4	47
8201011505	1 X 4.0	4.2	light blue	38.4	47
8201010905	1 X 4.0	4.2	orange	38.4	47
8201010805	1 X 4.0	4.2	pink	38.4	47
8201010405	1 X 4.0	4.2	red	38.4	47
8201010705	1 X 4.0	4.2	violet	38.4	47
8201010505	1 X 4.0	4.2	white	38.4	47
8201011105	1 X 4.0	4.2	yellow	38.4	47
8201010005	1 X 4.0	4.2	green-yellow	38.4	47
8201010106	1 X 6.0	5.1	black	57.6	70
8201010306	1 X 6.0	5.1	brown	57.6	70
8201010206	1 X 6.0	5.1	blue	57.6	70
8201011406	1 X 6.0	5.1	dark blue	57.6	70
8201011206	1 X 6.0	5.1	green	57.6	70
8201010606	1 X 6.0	5.1	grey	57.6	70
8201011506	1 X 6.0	5.1	light blue	57.6	70
8201010906	1 X 6.0	5.1	orange	57.6	70
8201010806	1 X 6.0	5.1	pink	57.6	70
8201010406	1 X 6.0	5.1	red	57.6	70
8201010706	1 X 6.0	5.1	violet	57.6	70
8201010506	1 X 6.0	5.1	white	57.6	70
8201011106	1 X 6.0	5.1	yellow	57.6	70
8201010006	1 X 6.0	5.1	green-yellow	57.6	70
8201010107	1 X 10.0	6.5	black	96	117
8201010307	1 X 10.0	6.5	brown	96	117
8201010207	1 X 10.0	6.5	blue	96	117
8201011407	1 X 10.0	6.5	dark blue	96	117

ÖLFLEX® UNIPLUS TRI

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Colour	Copper index (kg/km)	Weight (kg/km)
8201011207	1 X 10.0	6.5	green	96	117
8201010607	1 X 10.0	6.5	grey	96	117
8201011507	1 X 10.0	6.5	light blue	96	117
8201010907	1 X 10.0	6.5	orange	96	117
8201010807	1 X 10.0	6.5	pink	96	117
8201010407	1 X 10.0	6.5	red	96	117
8201010707	1 X 10.0	6.5	violet	96	117
8201010507	1 X 10.0	6.5	white	96	117
8201011107	1 X 10.0	6.5	yellow	96	117
8201010007	1 X 10.0	6.5	green-yellow	96	117
8201010108	1 X 16.0	7.5	black	153.6	172
8201010308	1 X 16.0	7.5	brown	153.6	172
8201010208	1 X 16.0	7.5	blue	153.6	172
8201011408	1 X 16.0	7.5	dark blue	153.6	172
8201011208	1 X 16.0	7.5	green	153.6	172
8201010608	1 X 16.0	7.5	grey	153.6	172
8201011508	1 X 16.0	7.5	light blue	153.6	172
8201010908	1 X 16.0	7.5	orange	153.6	172
8201010808	1 X 16.0	7.5	pink	153.6	172
8201010408	1 X 16.0	7.5	red	153.6	172
8201010708	1 X 16.0	7.5	violet	153.6	172
8201010508	1 X 16.0	7.5	white	153.6	172
8201011108	1 X 16.0	7.5	yellow	153.6	172
8201010008	1 X 16.0	7.5	green-yellow	153.6	172
8201010109	1 X 25.0	9.1	black	240	261
8201010309	1 X 25.0	9.1	brown	240	261
8201010209	1 X 25.0	9.1	blue	240	261
8201011409	1 X 25.0	9.1	dark blue	240	261
8201011209	1 X 25.0	9.1	green	240	261
8201010609	1 X 25.0	9.1	grey	240	261
8201011509	1 X 25.0	9.1	light blue	240	261
8201010909	1 X 25.0	9.1	orange	240	261
8201010809	1 X 25.0	9.1	pink	240	261
8201010409	1 X 25.0	9.1	red	240	261

ÖLFLEX® UNIPLUS TRI

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Colour	Copper index (kg/km)	Weight (kg/km)
8201010709	1 X 25.0	9.1	violet	240	261
8201010509	1 X 25.0	9.1	white	240	261
8201011109	1 X 25.0	9.1	yellow	240	261
8201010009	1 X 25.0	9.1	green-yellow	240	261
8201010110	1 X 35.0	10.2	black	336	353
8201010310	1 X 35.0	10.2	brown	336	353
8201010210	1 X 35.0	10.2	blue	336	353
8201011410	1 X 35.0	10.2	dark blue	336	353
8201011210	1 X 35.0	10.2	green	336	353
8201010610	1 X 35.0	10.2	grey	336	353
8201011510	1 X 35.0	10.2	light blue	336	353
8201010910	1 X 35.0	10.2	orange	336	353
8201010810	1 X 35.0	10.2	pink	336	353
8201010410	1 X 35.0	10.2	red	336	353
8201010710	1 X 35.0	10.2	violet	336	353
8201010510	1 X 35.0	10.2	white	336	353
8201011110	1 X 35.0	10.2	yellow	336	353
8201010010	1 X 35.0	10.2	green-yellow	336	353
8201010111	1 X 50.0	12.5	black	480	514
8201010311	1 X 50.0	12.5	brown	480	514
8201010211	1 X 50.0	12.5	blue	480	514
8201011411	1 X 50.0	12.5	dark blue	480	514
8201011211	1 X 50.0	12.5	green	480	514
8201010611	1 X 50.0	12.5	grey	480	514
8201011511	1 X 50.0	12.5	light blue	480	514
8201010911	1 X 50.0	12.5	orange	480	514
8201010811	1 X 50.0	12.5	pink	480	514
8201010411	1 X 50.0	12.5	red	480	514
8201010711	1 X 50.0	12.5	violet	480	514
8201010511	1 X 50.0	12.5	white	480	514
8201011111	1 X 50.0	12.5	yellow	480	514
8201010011	1 X 50.0	12.5	green-yellow	480	514