

## CHARGE M2 TFP/T2C S

Charge charging cable with type 2 connector and In cable control box for direct connection to a type F socket

### Info

Harnessing with In-Cable Control Box for charging mode 2 for electric vehicles with type 2 vehicle inlet



e-Mobility



Suitable for outdoor use



Cold-resistant



Mechanical resistance



Oil-resistant



Robust



UV-resistant

### Benefits

Resistant to microbes

Resistant to oil, dust and water

Special cable design for a long service life

Flexible at low temperatures

Withstands high mechanical stress, in particular abrasion and sliding demands

### Application range

Last Update (30.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## CHARGE M2 TFP/T2C S

For charging stations, electric and Plug-in Hybrid vehicles

### Product features

Charging current from 6-13A in 5 steps  
Monitoring of protective earth conductor  
PUR outer sheath  
Suitable for all weather conditions

### Product Make-up

H07BQ-F: Cable from Typ F plug up to ICCB  
Type 2 connectors are injection moulded in two-components process for optimal ergonomics  
Type F cable connectors are injection moulded

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC002839 ETIM 5.0 Class-Description: Accessories for battery/charger
Certifications:	according to VDE-AR-E2283-5 according to EN 61851-1
Temperature range:	Flexing: -30°C to +50°C

### Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Further colour combinations and lengths on request

**CHARGE M2 TFP/T2C S**

Article number	Version	Effective length (mm)	Copper index kg/1.000 pieces	Weight (kg/1000 pieces)	PU
Plug type F, charging cable with ICCB, vehicle connector type 2					
74880085	Charging: 1-phase 13A	4000	388	2570	1