

SILVYN® COMPACT M

Nickel-plated brass fitting with space-saving dimensions in various designs

SILVYN® COMPACT M is a nickel-plated brass conduit fitting with polished surface that offers IP67 protection

Info

Space-saving due to compact dimensions.



Mechanical resistance



Low weight



Space requirement



Robust



Temperature-resistant

Benefits

Space-saving application
For high mechanical stress
High tensile strength
Corrosion-resistant

Application range

In combination with protective conduit:
Suitable for SILVYN® HTDL/EF/OR/HCX/HFX
Mechanical engineering
Railway applications

Last Update (26.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® COMPACT M

Product Make-up

Metric connection thread
Hexagonal collar
Threaded sleeve
Cap nut

Note

PG threaded versions are to be found in the online catalogue

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001180 ETIM 5.0 Class-Description: Screw connection for protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001180 ETIM 6.0 Class-Description: Screw connection for protective metallic hose
Norm references / Approvals:	UL 514B
On request:	Available in stainless steel
Material:	Body: nickel-plated brass Sealing: polyamide O-ring: NBR
Protection rating:	IP 66 IP 67
Temperature range:	-45°C to +105°C

Note

* Trade product, no Lapp product

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® COMPACT M

Article number	Metric size	Suitable for SILVYN® HTDL/EF/OR/HCX/HFX	Suitable for SILVYN® HIPROJACKET	Pieces / PU
61803800	16 x 1.5	3/8"	13	10
61803801	20 x 1.5	3/8"	-	10
61803802	20 x 1.5	1/2"	16	10
61803803	25 x 1.5	3/4"	22	5
61803804	32 x 1.5	1"	25	5
61803805	40 x 1.5	1 1/4"	35	2
61803806	50 x 1.5	1 1/2"	38	2
61803807	63 x 1.5	2"	51	2
61803850	16 x 1.5	3/8"	13	10
61803851	20 x 1.5	3/8"	-	10
61803852	20 x 1.5	1/2"	16	10
61803853	25 x 1.5	3/4"	22	5
61803854	32 x 1.5	1"	25	5
SILVYN® COMPACT 90° M				
61803808	16 x 1.5	3/8"	13	10
61803809	20 x 1.5	3/8"	-	10
61803810	20 x 1.5	1/2"	16	10
61803811	25 x 1.5	3/4"	22	5
61803812	32 x 1.5	1"	25	5
61803813	40 x 1.5	1 1/4"	35	2
61803814	50 x 1.5	1 1/2"	38	2
61803815	63 x 1.5	2"	51	2

Last Update (26.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16