

SILVYN® COMPACT NPT

Nickel-plated brass fitting with space-saving dimensions in various designs

SILVYN® COMPACT NPT - nickel-plated brass conduit fitting with polished surface that offers IP67 protection

Info

Space-saving due to compact dimensions.



Mechanical resistance



Low weight



Space requirement



Robust



Temperature-resistant

Benefits

Space-saving application
For high mechanical stress
High tensile strength
Corrosion-resistant

Application range

In combination with protective conduit:
Suitable for SILVYN® HTDL/EF/OR/HCX/HFX
Mechanical engineering
Railway applications

Last Update (21.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® COMPACT NPT

Product Make-up

NPT connection thread
Hexagonal collar
Threaded sleeve
Cap nut

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001180 ETIM 5.0 Class-Description: Screw connection for protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001180 ETIM 6.0 Class-Description: Screw connection for protective metallic hose
Norm references / Approvals:	UL 514B
Material:	Body: nickel-plated brass Sealing: polyamide O-ring: NBR
Protection rating:	IP 67
Temperature range:	-45°C to +105°C

Note

* Trade product, no Lapp product

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® COMPACT NPT

Article number	NPT size	Suitable for SILVYN® HTDL/EF/OR/HCX/HFX	Suitable for SILVYN® HIPROJACKET	Pieces / PU
SILVYN® COMPACT NPT				
61803832	1/2"	3/8"	13	10
61803833	1/2"	1/2"	16	10
61803834	3/4"	3/4"	22	5
61803835	1"	1"	25	5
61803836	1 1/4"	1 1/4"	35	2
61803837	1 1/2"	1 1/2"	38	2
61803838	2"	2"	51	2
SILVYN® COMPACT 90° NPT				
61803839	1/2"	3/8"	13	10
61803840	1/2"	1/2"	16	10
61803841	3/4"	3/4"	22	5
61803842	1"	1"	25	5
61803843	1 1/4"	1 1/4"	35	2
61803844	1 1/2"	1 1/2"	38	2
61803845	2"	2"	51	2