

SILVYN® LTP 45° M

SILVYN® LTPW-M is a nickel-plated brass conduit fitting that offers a protection degree up to IP66/67/68/69



Benefits

- High tensile strength
- Vibration protection
- High sealing performance

Application range

- In combination with protective conduit: SILVYN® LTP
- Applications with high mechanical stress
- Used in areas where liquids are present

Product Make-up

- Metric connection thread
- 45° elbow, hexagonal collar
- Threaded sleeve
- Cap nut

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001180

ETIM 5.0 Class-Description: Screw connection for protective metallic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001180

ETIM 6.0 Class-Description: Screw connection for protective metallic hose

Certifications:

IEC EN 61386-23

Material:

Body: nickel-plated brass
Seal: PA compression seal

Protection rating:

IP66
IP67
IP68 (5 bar)

Last Update (31.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® LTP 45° M

IP69

Temperature range:

-50°C to +135°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® LTP 45° M

Article number	Metric size	SW wrench size mm	Thread length mm	Suitable for SILVYN® LTP	Pieces / PU
SILVYN® LTP 45° M					
55510300	20 x 1.5/1	24.0	13	16	10
55510301	20 x 1.5/2	24.0	13	20	10
55510302	25 x 1.5	30.0	14	25	10
55510303	32 x 1.5	36.0	15	32	2
55510304	40 x 1.5	47.0	18	40	1
55510305	50 x 1.5	61.0	18	50	1
55510306	63 x 1.5	67.0	20	63	1