


SILVYN® LCC-E

SILVYN® LCC-E - nickel-plated brass insert

Info

Ensuring cables do not get damaged



Reliability



Temperature-resistant

Benefits

Cable damage can be prevented

Application range

Conduit end cover

If no conduit fitting is used

Product features

All-round collar completely covers the protective conduit end

Product Make-up

Threaded sleeve

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000519

ETIM 5.0 Class-Description: Terminal sleeve for protective hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000519

ETIM 6.0 Class-Description: Terminal sleeve for protective hose

Material:

Nickel-plated brass

Last Update (23.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® LCC-E

Temperature range: -50 °C to +135 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® LCC-E

Article number	Nominal size	Suitable for SILVYN® LCC-2 / LCCH-2	Pieces / PU
SILVYN® LCC-E			
61805600	10	10	10
61805610	12	12	10
61805620	16	16	10
61805630	20	20	10
61805640	25	25	10
61805650	32	32	10
61805660	40	40	10
61805670	50	50	4
61805680	63	63	1
61805690	75	75	1