


SILVYN® LGF-2-M

SILVYN® LGF-2-M is a nickel-plated brass conduit fitting for usage in fixed installations



Corrosion-resistant



Mechanical resistance



Oil-resistant



Space requirement



Robust



Temperature-resistant

Benefits

For fixed applications

High tensile strength

Space-saving

Application range

In combination with protective conduit:

SILVYN® LCC-2

SILVYN® LCCH-2

Applications with high mechanical stress

Outdoors

Product Make-up

Metric connection thread

Last Update (26.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® LGF-2-M

Hexagonal collar
Cap nut

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001180 ETIM 5.0 Class-Description: Screw connection for protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001180 ETIM 6.0 Class-Description: Screw connection for protective metallic hose
Norm references / Approvals:	IEC EN 61386-23
Material:	Nickel-plated brass
Protection rating:	IP 54
Temperature range:	-50 °C to +300 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® LGF-2-M

Article number	Metric size	SW wrench size mm	Overall length mm	Thread length mm	Suitable for SILVYN® LCC-2 / LCCH-2	Pieces / PU
SILVYN® LGF-2-M						
55501981	12 x 1.5	13	21	8	10	10
55502001	16 x 1.5/1	17	23	8	12	10
55502002	16 x 1.5/2	20	25	10	16	10
55502021	20 x 1.5/1	22	25	10	16	10
55502022	20 x 1.5/2	24	26.3	10	20	10
55502031	25 x 1.5	29	32.5	10	25	10
55502041	32 x 1.5	38	36.8	13	32	10
55502051	40 x 1.5	48	39	14	40	4
55502061	50 x 1.5	58	42	15	50	4
55502071	63 x 1.5	70	50	18	63	1
55502073	75 x 1,5	84	60	20	75	1