


SILVYN® LGS-2-M

SILVYN® LGS-2-M is a swivelling nickel-plated brass conduit fitting for installation with torsional movements



Corrosion-resistant



Mechanical resistance



Oil-resistant



Space requirement



Robust

Benefits

For rotating applications

High tensile strength

Space-saving

Application range

In combination with protective conduit:

SILVYN® LCC-2

SILVYN® LCCH-2

Applications with high mechanical stress

Outdoors

Product Make-up

Metric connection thread

Hexagonal collar with torsion element

Cap nut

Last Update (27.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® LGS-2-M

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001180

ETIM 5.0 Class-Description: Screw connection for protective metallic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001180

ETIM 6.0 Class-Description: Screw connection for protective metallic hose

Material:

Nickel-plated brass

Protection rating:

IP 54

Temperature range:

-50 °C to +300 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® LGS-2-M

Article number	Metric size	SW wrench size mm	Overall length mm	Thread length mm	Suitable for SILVYN® LCC-2 / LCCH-2	Pieces / PU
SILVYN® LGS-2-M						
55501982	12 x 1.5	13	30.2	8	10	10
55502003	16 x 1.5/1	17	32.2	8	12	10
55502004	16 x 1.5/2	20	34.2	10	16	10
55502023	20 x 1.5/1	22	34.2	10	16	10
55502024	20 x 1.5/2	24	35.5	10	20	10
55502032	25 x 1.5	29	43.7	10	25	10
55502042	32 x 1.5	38	48	13	32	10
55502052	40 x 1.5	48	51.2	14	40	4
55502062	50 x 1.5	58	54.2	15	50	4
55502072	63 x 1.5	70	63.2	18	63	1