


SILVYN® UI COMPACT M

SILVYN® UI COMPACT M - nickel-plated brass conduit fitting for use with SILVYN® UI 511

Info

Space-saving due to compact dimensions.



Good chemical resistance



Corrosion-resistant



Mechanical resistance



Robust



Reliability



Temperature-resistant



UV-resistant

Benefits

High chemical-resistance
For high mechanical stress
High tensile strength
Corrosion-resistant

Application range

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® UI COMPACT M

In combination with protective conduit:
SILVYN® UI 511

Product Make-up

Metric connection thread
Hexagonal collar
Threaded sleeve
Cap nut

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001180

ETIM 5.0 Class-Description: Screw connection for protective metallic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001180

ETIM 6.0 Class-Description: Screw connection for protective metallic hose

Material:

Stainless steel AISI 304

DW no. 1.4301

Nickel-plated brass

Protection rating:

IP 40

Temperature range:

-45 °C to +105 °C (with O-Ring)

-55 °C to +260 °C (without O-Ring)

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® UI COMPACT M

Article number	Metric size	Clear opening (mm)	Suitable for SILVYN® UI 511	Pieces / PU
SILVYN® UI COMPACT M (stainless steel)				
61803880	16 x 1.5	9.8	3/8"	1
61803881	20 x 1.5/1	9.8	3/8"	1
61803882	20 x 1.5/2	13.9	1/2"	1
61803883	25 x 1.5	18.5	3/4"	1
61803884	32 x 1.5	22.8	1"	1
61803885	40 x 1.5	30.8	1 1/4"	1
61803886	50 x 1.5	36.8	1 1/2"	1
61803887	63 x 1.5	47.8	2"	1
SILVYN® UI COMPACT M (nickel-plated brass)				
61803870	16 x 1.5/1	6.8	5/16"	1
61803871	16 x 1.5/2	9.8	3/8"	1
61803872	20 x 1.5/1	6.8	5/16"	1
61803873	20 x 1.5/2	9.8	3/8"	1
61803874	20 x 1.5/3	13.9	1/2"	1
61803875	25 x 1.5	18.5	3/4"	1
61803876	32 x 1.5	22.8	1"	1
61803877	40 x 1.5	30.8	1 1/4"	1
61803878	50 x 1.5	36.9	1 1/2"	1
61803879	63 x 1.5	47.9	2"	1